EPIC® H-B 16 TGH 2X


Housing design H-B. The industry standard.

The robust high metal housing with a direct cable entry is suitable for use in investment construction.

Info

Non-slip ridges for comfortable disconnecting
For easy introduction of two cables
NEMA 250, UL50E: 12, 4 (latched)





Supplementary automation components from Lapp

Mechanical and plant engineering

Mechanical resistance

Robust

Waterproof

Benefits

The housing standard. Wide choice for all applications
More interior space for wiring

Application range

Plant engineering
Light & sound technology
Plastics industry

©2023 Lapp Group - Technical changes reserved

EPIC® H-B 16 TGH 2X

Product features

Hood, high version
Bolts for double lever
2 straight cable entries
Versions without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2023 Lapp Group - Technical changes reserved

LAPP

EPIC® H-B 16 TGH 2X

PRODUCT INFORMATION

Article number	Article description	M	Pieces / PU
H-B housing: hood (2 straight cable entries, bolts for double lever, high version)			
44422018	H-B 16 TGH 2XM25	2 x 25	5
79128600	H-B 16 TGH 2XM32	2 x 32	5

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16