EPIC® H-B 16 TSH

Housing design H-B. The industry standard.


The robust metal housing is suitable for use in the plastics industry and is available with or without a neck.

Info

Non-slip ridges for comfortable disconnecting
More interior space for wiring
Protection rating UL50E tested







Supplementary automation components from Lapp

Mechanical and plant engineering

Mechanical resistance

Robust

Waterproof

Benefits

The housing standard. Wide choice for all applications
M40 housing extension on M50 with SKINTOP 53112083 possible (clamping range 27 - 35 mm)

Application range

Plant engineering
Light & sound technology
Plastics industry

Last Update (23.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-B 16 TSH

Product features

Hood, high version
Bolts for double lever
Side cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2024 Lapp Group - Technical changes reserved

LAPP

EPIC® H-B 16 TSH

PRODUCT INFORMATION

Article number	Article description	M	PG	Neck	Pieces / PU
H-B housing: hood (side cable entry, bolts for double lever, high version)					
70102200	H-B 16 TSH 21	-	21	yes	5
70102400	H-B 16 TSH 29	-	29	yes	5
79102200	H-B 16 TSH M25	25	-	-	5
79102400	H-B 16 TSH M32	32	-	-	5
79102800	H-B 16 TSH M40	40	-	-	5

Last Update (23.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16