

## EPIC® MC module: HC3

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

The power and signal module can be combined in one housing and is suitable for printing presses and investment construction.

### Info

Very high current transfer in a small space



Supplementary automation components from Lapp



Mechanical and plant engineering



Wind Energy

### Benefits

The mix of different functions in one plug guarantees high flexibility  
Assembly of individual connectors, suitable for different applications

### Application range

Plant engineering  
Printing machines  
Control engineering

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002641

ETIM 5.0 Class-Description: Modular connector (industrial connector)

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002641

ETIM 6.0 Class-Description: Modular connector (industrial connector)

Rated voltage (V):

IEC: 1000 V AC/DC

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® MC module: HC3

	UL: 600 V AC/DC
Rated current (A):	50 A
Pollution degree:	3
Contact resistance:	< 2 mOhm
Contacts:	Copper alloy, hard silver-plated
Number of contacts:	3
Termination methods:	Crimp termination: 1.5 - 10 mm <sup>2</sup>
Cycle of mechanical operation:	100
VDE-tested:	UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® MC module: HC3**

Article number	Article description	Contact type	Number of operating contacts	Slots	Pieces / PU
Module: high voltage 3-pin					
10399800	MCS 3 CM-HV	male	3	1	10
10399900	MCB 3 CM-HV	female	3	1	10