

## EPIC® MC Module Pneumatic 1pole

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

The pneumatic module with valve is suitable for 2.5 and 4 mm hoses and has one brass contact. It is suitable for use in printing presses.

### Info

Pneumatic modules with valve for 2.5 und 4mm tubings



Supplementary automation components from Lapp



Mechanical and plant engineering



Wind Energy

### Benefits

The mix of different functions in one plug guarantees high flexibility  
Assembly of individual connectors, suitable for different applications

### Application range

Plant engineering  
Printing machines  
Control engineering

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002641

ETIM 5.0 Class-Description: Modular connector (industrial connector)

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002641

ETIM 6.0 Class-Description: Modular connector (industrial connector)

Contacts:

Brass

Number of contacts:

1

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® MC Module Pneumatic 1pole

Termination methods:	Plug-in connection: for hose with inner diameter 2.5 mm/4.0 mm
Cycle of mechanical operation:	100
Operating pressure:	8 bar
Testing pressure:	10 bar
Temperature range:	-20 °C to +100 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

## EPIC® MC Module Pneumatic 1 pole

Article number	Article description	Contact type	Number of operating contacts	Slots	Pieces / PU
Module: pneumatic 1-pin					
44424004	MCS 1x2,5 PNEU (10)	male	1	1	10
44424005	MCB 1x2,5 PNEU (10)	female with valve	1	1	10
44424006	MCS 1x4,0 PNEU (10)	male	1	1	10
44424007	MCB 1x4,0 PNEU (10)	female with valve	1	1	10

## EPIC® MC Module Pneumatic 1pole

