


EPIC® TB-H-BE 24

For convenient, clear wiring in control cabinets.
Assembly in panel-mount base housings.

The standard insert can be connected with H-BE pin inserts in housing and is suitable for use in control cabinets and investment construction.

Info

Plug connection for control cabinets



Benefits

Standard H-BE inserts for use with switch cabinets

Pluggable with H-BE male inserts in hoods

Fastening on side = "left" means that when mounting the terminal adapter on the left wall of a control cabinet, the PE connection and pin "1" are on the "top" side

Application range

Control cabinet manufacturing

Plant engineering

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000438

ETIM 5.0 Class-Description: Contact insert for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000438

ETIM 6.0 Class-Description: Contact insert for industrial connectors

Rated voltage (V):

IEC: 500 VUL: 600 VCSA: 600 V

Rated impulse voltage:

6 kV

Rated current (A):

IEC: 16 A
UL: 16 A
CSA: 16 A

Pollution degree:

3

Last Update (30.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® TB-H-BE 24

| | |
|--------------------------------|--|
| Contacts: | Copper alloy, hard silver-plated |
| Number of contacts: | 24 + PE |
| Termination methods: | Screw termination: 0.5 - 4.0 mm ² |
| Stripping length (mm): | 13 |
| Cycle of mechanical operation: | 200 |
| VDE-tested: | UL-tested: UL File Number: E75770 |
| Temperature range: | -40 °C to +100 °C, short-term up to +125 °C |

Note

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® TB-H-BE 24

| Article number | Article description | Contact type | Fastening on side | Number of operating contacts | Pieces / PU |
|-------------------------|---------------------|--------------|-------------------|------------------------------|-------------|
| 24-pin terminal adapter | | | | | |
| 70317100 | TB-H-BE 24 BRE | female | right | 1 - 24 | 10 |
| 70316100 | TB-H-BE 24 BLI | female | left | 1 - 24 | 10 |

EPIC® TB-H-BE 24