

EPIC® ULTRA H-A 3 TS

The robust and reliable industry connector housing as EMC version

EPIC® Rectangular connector housing EMC protection, corrosion resistant, UL50E, Nema250

Info

EMC protection
Corrosion-resistant
Made in Germany



Supplementary automation components from Lapp



Food & Beverage



Mechanical and plant engineering



Rail



Wind Energy



Suitable for outdoor use



Good chemical resistance



Corrosion-resistant

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® ULTRA H-A 3 TS



Mechanical resistance



Space requirement



Robust



Interference signals



Waterproof

Benefits

The arrow as a new design element on the surface of the housing is easy to feel and simplifies plugging in spatially confined and possibly poorly visible application areas.

The EPIC® ULTRA H-A 3 range comprises the smallest EMC housings in the heavy-duty industrial connector sector and ensures safe plug connections in a small amount of space.

The hood housing is mateable with many commercially available housings (panel-mount base, surface-mount base or coupler hood housings).

Space-saving due to compact dimensions.

Corresponds to protection class IP 65 when locked.

Protection class classified according to NEMA 250 as well as tested according to UL50E.

Application range

To protect the connector insert from environmental influences.

Especially for environments where the product is getting into contact with water, cleaning agents and saline substances.

Especially for environments where electromagnetic compatibility (EMC) is required.

For use with many EPIC® rectangular connector inserts.

Withstands high environmental and mechanical stresses.

Product features

Resistance to cyclic salt spray is tested according to IEC 68-2-52, severity level 2

Salt spray testing according to DIN EN ISO 9227, method NSS, period of test 480 hours

Corrosion-resistant according to DIN EN 6988

Delivery including stainless steel screw for the inserts

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Zinc die-cast, nickel-plated
Protection rating:	IP 65 NEMA 250, UL50E: 12, 4, 4X (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40°C to +100°C, short-term up to +125°C

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® ULTRA H-A 3 TS

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



EPIC® ULTRA H-A 3 TS

Article number	Article description	M	Pieces / PU
10423201	EPIC® ULTRA H-A 3 TS	20	10

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16