

## EPIC® H-B 24 TBFH-LB

Housing design H-B. The industry standard.

The robust metal housing with a single lever and a direct cable entry is ideal for use in the plastics industry and for investment construction applications.

### Info

More interior space for wiring

Single Lever version for quick locking and simple unlocking with lifting aid

Protection rating UL50E tested



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

### Benefits

Safe fixing with 4 screws

Casted neck for easy assembly of the cable gland

### Application range

Plant engineering

Light & sound technology

Plastics industry

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® H-B 24 TBFH-LB

### Product features

Cable coupler hood, high version  
Single lever  
Straight cable entry  
Versions with / without neck

### Technical Data

|                        |  |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000437<br>ETIM 5.0 Class-Description: Housing for industrial connectors |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000437<br>ETIM 6.0 Class-Description: Housing for industrial connectors |
| Material:              | Housing: powder-coated aluminium alloy, grey<br>Lever: zinc-plated steel<br>Sealing: NBR     |
| Protection rating:     | IP 65 (latched)<br>NEMA 250, UL50E: 12 (latched)   |
| VDE-tested:            | Certified production control: VDE-REG. no.: B437<br>UL-tested:<br>UL File Number: E75770     |
| Temperature range:     | -40 °C to +100 °C, short-term up to +125 °C  |

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® H-B 24 TBFH-LB**

| Article number   | Article description | M  | PG | Neck | Pieces / PU |
|--|---------------------|----|----|------|-------------|
| H-B housing: cable coupler hood (1 straight cable entry, single lever, high version) |                     |    |    |      |             |
| 70142400   | H-B 24 TBFH-LB 21   | -  | 21 | yes  | 5           |
| 79142400   | H-B 24 TBFH-LB M25  | 25 | -  | -    | 5           |
| 79142600   | H-B 24 TBFH-LB M32  | 32 | -  | -    | 5           |