

EPIC® H-B 24 TSB

Housing design H-B. The industry standard.


The robust metal housing with 2 double levers, a side cable entry and a neck is suitable for use in investment construction.

Info

Non-slip ridges for comfortable disconnecting

For connection with counterpart with integrated cover

Protection rating UL50E tested



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

Ideal for many applications due to a wide range of housings and inserts

Double lever version with 2 levers for increased safety

Application range

Plant engineering

Light & sound technology

Plastics industry

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 24 TSB

Product features

Hood, low version
Dual levers
Side cable entry
Versions with neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 24 TSB

Article number	Article description	M	PG	Neck	Pieces / PU
H-B housing: hood (side cable entry, double lever)					
10114000	H-B 24 TSB 21	-	21	yes	5
10124000	H-B 24 TSB 29	-	29	yes	5
19114000	H-B 24 TSB M25	25	-	yes	5
19124000	H-B 24 TSB M32	32	-	yes	5