


FLEXIMARK® TA foam Component marking

FLEXIMARK® Labels are markers made of polyester foam and are an inexpensive alternative for engraved plastic markers for component marking in the electrical industry (e.g. marking cabinets).

Info

Included in FLEXIMARK® sample bag (article no. M3251010)



Mechanical and plant engineering



Good chemical resistance



Halogen-free



Assembly time



UV-resistant

Benefits

Good UV-resistance

Self-adhesive on many surfaces

Cost-efficient alternative to traditionally used engraved plastic signs

Application range

Identification of electrical components, panels, push buttons and information signs

Note

Easy to print via FLEXIMARK® software Flexisoft and FLEXIMARK® thermal transfer printer SQUIX, EOS5 or EOS2

Recommended ribbon: FTI-Y 60-360 BK (article no. 83260201)

Included

Delivered as a roll of labels

Last Update (27.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® TA foam Component marking

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001288 ETIM 5.0 Class-Description: Labelling material
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001288 ETIM 6.0 Class-Description: Labelling material
Adhesive:	Acrylic-based permanent adhesive
Colour delivered:	Silver White in web catalogue
Material:	Polyester foam
Temperature range:	-40 °C to +90 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® TA foam Component marking

Article number	Article designation	Colour	Width (mm)	Length (mm)	Markers / PU	PU
83260166	FLEXIMARK® TA foam 27-12.5 SR	silver	12.5	27	1000	1
83260167	FLEXIMARK® TA foam 27-15 SR	silver	15	27	1000	1
83260168	FLEXIMARK® TA foam 27-18 SR	silver	18	27	1000	1
83260170	FLEXIMARK® TA foam 30-40 SR	silver	40	30	1000	1
83260171	FLEXIMARK® TA foam 35-15 SR	silver	15	35	1000	1
83260172	FLEXIMARK® TA foam 35-18 SR	silver	18	35	1000	1
83260173	FLEXIMARK® TA foam 45-15 SR	silver	15	45	1000	1
83260176	FLEXIMARK® TA foam 50-15 SR	silver	15	50	1000	1
83260177	FLEXIMARK® TA foam 50-25 SR	silver	25	50	750	1
83260179	FLEXIMARK® TA foam 60-30 SR	silver	30	60	500	1
83260180	FLEXIMARK® TA foam 70-18 SR	silver	18	70	1000	1
83260182	FLEXIMARK® TA foam 90-30 SR	silver	30	90	250	1
83260183	FLEXIMARK® TA foam 90-45 SR	silver	45	90	250	1
83260185	FLEXIMARK® TA foam 100-30 SR	silver	30	100	250	1
83260186	FLEXIMARK® TA foam 100-50 SR	silver	50	100	250	1
83260188	FLEXIMARK® TA foam 105-140 SR	silver	140	105	250	1
83260164	FLEXIMARK® TA foam 27-8 WH	white	8	27	1000	1
83260169	FLEXIMARK® TA foam 27-18 WH	white	18	27	1000	1
83260165	FLEXIMARK® TA foam 27-12.5 WH	white	12.5	27	1000	1
83260174	FLEXIMARK® TA foam 45-15 WH	white	15	45	1000	1
83260175	FLEXIMARK® TA foam	white	19	48	1000	1

FLEXIMARK® TA foam Component marking

Article number	Article designation	Colour	Width (mm)	Length (mm)	Markers / PU	PU
	48-19 WH					
83260178	FLEXIMARK® TA foam 60-30 WH	white	30	60	500	1
83260181	FLEXIMARK® TA foam 90-30 WH	white	30	90	250	1
83260184	FLEXIMARK® TA foam 90-45 WH	white	45	90	250	1
83260187	FLEXIMARK® TA foam 100-50 WH	white	50	100	250	1
Round cut-out						
83260189	FLEXIMARK® TA foam 40-30 Ø 24mm SR	silver	30	40	1000	1
83260190	FLEXIMARK® TA foam 40-30 Ø 24mm WH	white	30	40	1000	1