

EPIC® H-B 6 TS


Housing design H-B. The industry standard.






The universal robust housing for rectangular connectors has a side cable entry, pivots for a single lever and can be used, for example, in control systems.

Info

Non-slip ridges for comfortable disconnecting

Protection rating UL50E tested



-  Supplementary automation components from Lapp
-  Mechanical and plant engineering
-  Mechanical resistance
-  Robust
-  Waterproof

Benefits

The smallest housing out of the H-B series. For inserts with high electrical properties

Application range

Plant engineering
Control engineering
Plastics industry

Product features

Hood, low version

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 6 TS

Bolts for single lever
Side cable entry
Versions with neck

Technical Data

| | |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors |
| Material: | Housing: powder-coated aluminium alloy, grey Bolts: steel, coated |
| Protection rating: | IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched) |
| VDE-tested: | Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770 |
| Temperature range: | -40°C to +100°C, short-term up to +125°C |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 6 TS

| Article number | Article description | M | PG | Neck | Pieces / PU |
|--|---------------------|----|------|------|-------------|
| H-B housing: hood (side cable entry, bolts for single lever) | | | | | |
| 10012000 | H-B 6 TS 13,5 | - | 13.5 | yes | 10 |
| 10022000 | H-B 6 TS 16 | - | 16 | yes | 10 |
| 19012000 | H-B 6 TS M20 | 20 | - | yes | 10 |
| 19022000 | H-B 6 TS M25 | 25 | - | yes | 10 |