

EPIC® H-D 64 stamped


Multi-pole inserts for stamped crimp contacts

The connector insert with 64 pressed contacts is suitable for rectangular connectors in lighting and sound systems.

Info
for automated production with crimping machine
Suitable for processing with contacts on reel
Made in Europe







Mechanical and plant engineering

Space requirement

Robust

Benefits
Inserts of the connector series H-D are designed for applications in which a high number of contacts are required.

Application range
Plant engineering
Light & sound technology

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000438 ETIM 5.0 Class-Description: Contact insert for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000438 ETIM 6.0 Class-Description: Contact insert for industrial connectors

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-D 64 stamped

Rated voltage (V):	IEC: 250 V UL: 250 V
Rated impulse voltage:	2.5 kV
Rated current (A):	IEC: 10 A UL: 10 A
Pollution degree:	3
Contact resistance:	< 2 mOhm
Contacts:	Copper alloy, hard silver/gold-plated
Number of contacts:	64 + PE
Termination methods:	Crimp termination: 0.14 - 2.5 mm^2
Cycle of mechanical operation:	100
Certifications:	UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2023 Lapp Group - Technical changes reserved

EPIC® H-D 64 stamped

Article number	Article description	Contact type	Article designation	Number of operating contacts	Pieces / PU
11270000	H-D 64 SCG	male	stamped	1 - 64	5
11271000	H-D 64 BCG	female	stamped	1 - 64	5

©2023 Lapp Group - Technical changes reserved