

## EPIC® MC Module: 3pole

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

The three-pole signal module contains 3 contacts and is suitable for use in control systems, investment construction and printing presses.

### Info

Very high current transfer in a small space



Supplementary automation components from Lapp



Mechanical and plant engineering



Wind Energy

### Benefits

The mix of different functions in one plug guarantees high flexibility  
Assembly of individual connectors, suitable for different applications

### Application range

Plant engineering  
Printing machines  
Control engineering

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002641

ETIM 5.0 Class-Description: Modular connector (industrial connector)

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002641

ETIM 6.0 Class-Description: Modular connector (industrial connector)

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® MC Module: 3pole

Rated voltage (V):	630 V
Rated current (A):	40
Pollution degree:	3
Contact resistance:	< 2 mOhm
Contacts:	Copper alloy, hard silver-plated
Number of contacts:	3
Termination methods:	Crimp termination: 1.5 - 10 mm <sup>2</sup>
Cycle of mechanical operation:	100
VDE-tested:	UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

## EPIC® MC Module: 3pole

Article number	Article description	Contact type	Number of operating contacts	Slots	Pieces / PU
Module: 3-pin					
10382000	MCS 3 CM	male	3	1	10
10382100	MCB 3 CM	female	3	1	10