

EPIC® MC Module: 5pole

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

One housing can combine signal and power modules and therefore ensures high flexibility. This is suitable for control systems.



Supplementary automation components from Lapp



Mechanical and plant engineering



Wind Energy

Benefits

The mix of different functions in one plug guarantees high flexibility
Assembly of individual connectors, suitable for different applications

Application range

Plant engineering
Printing machines
Control engineering

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002641

ETIM 5.0 Class-Description: Modular connector (industrial connector)

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002641

ETIM 6.0 Class-Description: Modular connector (industrial connector)

Rated voltage (V):

400 V

Rated current (A):

20 A

Pollution degree:

3

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® MC Module: 5pole

Contact resistance:	< 2 mOhm
Contacts:	Copper alloy, hard silver-plated
Number of contacts:	5
Termination methods:	Crimp termination: 0.5 - 4.0 mm ²
Cycle of mechanical operation:	100
VDE-tested:	UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MC Module: 5pole

Article number	Article description	Contact type	Number of operating contacts	Slots	Pieces / PU
Module: 5-pin					
10382200	MCS 5 CM	male	5	1	10
10382300	MCB 5 CM	female	5	1	10