


## HITRONIC® HUN Universal Cable

Universal cable with central loose tube and non-metallic strain relief

HITRONIC® HUN Universal cable with central loose tube, rodent protection, dielectric A/J-DQ(ZN)BH or U-DQ(ZN)BH

### Info

CPR: Article number choice under [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)  
For indoor and outdoor use



Ethernet



Halogen-free



Heat-resistant



Low weight



Optimum strain relief



UV-resistant



Waterproof

### Benefits

Flame retardance makes it suitable for indoor and outdoor installations

Easy to install due to the compact design, high flexibility, robust sheath and small bending radii

UV-resistant

longitudinally and laterally watertight

Zero electromagnetic interference as the cable contains no metal (totally dielectric)

### Application range

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## HITRONIC® HUN Universal Cable

For indoor and outdoor use  
Campus backbone  
Industrial environments  
Methods of Deployment: empty plastic pipes, ducts and trays

### Product features

Central loose tube with up to 24 fibres  
Colour-coded fibres  
Longitudinal watertight  
Outer sheath flame-retardant and halogen-free  
Rodent-protection

### Product Make-up

Glass fibres with primary coating  
Gel-filled loose tube  
Water-blocking reinforced glass yarn strain relief  
LSZH outer sheath  
Colour: dark grey

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000034 ETIM 5.0 Class-Description: Fibre optic cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000034 ETIM 6.0 Class-Description: Fibre optic cable
Dimensions:	Primary coated fibre: 250µm Cable: see table
Core identification code:	Fibre colour code see data sheet
Fibre type:	GOF - Glass Optical Fibre
Standard designation:	A/J-DQ(ZN)BH U-DQ(ZN)BH
Optical values:	see data sheet
Optical fibre type:	Core material: glass Cladding material: glass
Permissible bending radius:	Static: $\geq 15 \times$ outer diameter Dynamic: $\geq 20 \times$ outer diameter
Permissible tensile force:	Fixed installation: 1500 N Short-term: 2000 N
Temperature range:	Fixed installation: -30 °C to +70 °C

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

The cables can also be supplied as pre-terminated fibre optic trunks.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**HITRONIC® HUN Universal Cable**

Article number	Article designation	Fibre type	Number of fibres	Outer diameter [mm]	Weight (kg/km)
<b>Multimode G 50 OM3</b>					
27400304	HITRONIC® HUN1500 4G 50/125 OM3	50/125 OM3	4	7.3	53
27400308	HITRONIC® HUN1500 8G 50/125 OM3	50/125 OM3	8	7.3	53
27400312	HITRONIC® HUN1500 12G 50/125 OM3	50/125 OM3	12	7.3	53
27400324	HITRONIC® HUN1500 24G 50/125 OM3	50/125 OM3	24	8.3	60
<b>Multimode G 50 OM3 - stranded loose tubes</b>					
26400324	HITRONIC® HUN1500 2x12G 50/125 OM3	50/125 OM3	24	10.1	84
26400348	HITRONIC® HUN1500 4x12G 50/125 OM3	50/125 OM3	48	11	109
<b>Multimode G 50 OM2</b>					
27400204	HITRONIC® HUN1500 4G 50/125 OM2	50/125 OM2	4	7.3	53
27400208	HITRONIC® HUN1500 8G 50/125 OM2	50/125 OM2	8	7.3	53
27400212	HITRONIC® HUN1500 12G 50/125 OM2	50/125 OM2	12	7.3	53
27400224	HITRONIC® HUN1500 24G 50/125 OM2	50/125 OM2	24	8.3	60
<b>Multimode G 62.5 OM1</b>					
27400104	HITRONIC® HUN1500 4G 62.5/125 OM1	62.5/125 OM1	4	7.3	53
27400108	HITRONIC® HUN1500 8G 62.5/125 OM1	62.5/125 OM1	8	7.3	53
27400112	HITRONIC® HUN1500 12G 62.5/125 OM1	62.5/125 OM1	12	7.3	53
27400124	HITRONIC® HUN1500 24G 62.5/125 OM1	62.5/125 OM1	24	8.3	60
<b>Single-mode E 9 OS2</b>					
27400904	HITRONIC® HUN1500 4E 9/125 OS2	9/125 OS2	4	7.3	53
27400908	HITRONIC® HUN1500 8E 9/125 OS2	9/125 OS2	8	7.3	53
27400912	HITRONIC® HUN1500 12E 9/125 OS2	9/125 OS2	12	7.3	53
27400924	HITRONIC® HUN1500 24E 9/125 OS2	9/125 OS2	24	8.3	60

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16

**HITRONIC® HUN Universal Cable**

Article number	Article designation	Fibre type	Number of fibres	Outer diameter [mm]	Weight (kg/km)
	9/125 OS2				
Single-mode E 9 OS2 - stranded loose tubes					
26400924	HITRONIC® HUN1500 2x12E 9/125 OS2	9/125 OS2	24	10.1	84
26400948	HITRONIC® HUN1500 4x12E 9/125 OS2	9/125 OS2	48	11	109
26400972	HITRONIC® HUN2000 6x12E 9/125 OS2	9/125 OS2	72	12.6	148
26400996	HITRONIC® HUN2000 8x12E 9/125 OS2	9/125 OS2	96	14.3	190
26400944	HITRONIC® HUN2000 12x12E 9/125 OS2	9/125 OS2	144	17	221

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16