


Marking rings PC

Open marking rings with pre-printed characters and numbers for marking wires/single cores after assembly, Snap-On mechanism, flame-retardant according to UL 94 V

Info

Accessories (storage box) available in the web catalogue



Flame-retardant



UV-resistant

Benefits

Open marking rings with pre-printed number or character

The shape ensures secure fixation to the cable, while the anti-rotation feature allows for a secure combination marking.

Good UV resistance

Easy mounting through clipping

Application range

For single core marking

Marking after assembly

Also possible to use for marking wires before assembly

Product features

Cross-section in mm²:

PC 10: 1

PC 20: 2.5

PC 30: 4

PC 40: 6

Diameter application area in mm:

PC 10: 2.4-3

PC 20: 3-4

PC 30: 4-5

PC 40: 5-6.2

Width x height mm / sleeve length mm:

PC 10: 3,7 x 3,6 / 3

PC 20: 4,5 x 4,2 / 3

PC 30: 5,7 x 5,5 / 3

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

Marking rings PC

PC 40: 6,9 x 6,7 / 4

Norm references / Approvals

Extremely flame-retardant according to
UL 94 V0

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001288 ETIM 5.0 Class-Description: Labelling material
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001288 ETIM 6.0 Class-Description: Labelling material
Colour delivered:	Yellow
Material:	Cadmium-free and silicon-free hard PVC
Temperature range:	-30°C to +60°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Marking rings PC

Article number	Article designation	Markers / PU	PU
PC 10			
61820900	PC 10 / O	200	1
61820910	PC 10 / 1	200	1
61820920	PC 10 / 2	200	1
61820930	PC 10 / 3	200	1
61820940	PC 10 / 4	200	1
61820950	PC 10 / 5	200	1
61820960	PC 10 / 6	200	1
61820970	PC 10 / 7	200	1
61820980	PC 10 / 8	200	1
61820990	PC 10 / 9	200	1
61821000	PC 10 / blank	200	1
61821010	PC 10 / A	200	1
61821020	PC 10 / B	200	1
61821030	PC 10 / C	200	1
61821040	PC 10 / D	200	1
61821050	PC 10 / E	200	1
61821060	PC 10 / F	200	1
61821070	PC 10 / G	200	1
61821080	PC 10 / H	200	1
61821090	PC 10 / I	200	1
61821100	PC 10 / J	200	1
61821110	PC 10 / K	200	1
61821120	PC 10 / L	200	1
61821130	PC 10 / M	200	1
61821140	PC 10 / N	200	1
61821150	PC 10 / O	200	1
61821160	PC 10 / P	200	1
61821170	PC 10 / Q	200	1
61821180	PC 10 / R	200	1
61821190	PC 10 / S	200	1
61821200	PC 10 / T	200	1
61821210	PC 10 / U	200	1
61821220	PC 10 / V	200	1
61821230	PC 10 / W	200	1

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

Marking rings PC

Article number	Article designation	Markers / PU	PU
61821240	PC 10 / X	200	1
61821250	PC 10 / Y	200	1
61821260	PC 10 / Z	200	1
61821270	PC 10 / /	200	1
61821280	PC 10 / .	200	1
61821290	PC 10 / ,	200	1
61821300	PC 10 / :	200	1
61821310	PC 10 / =	200	1
61821320	PC 10 / earth	200	1
61821360	PC 10 / +	200	1
61821370	PC 10 / -	200	1
61821380	PC 10 / ~	200	1
PC 20			
61821400	PC 20 / 0	200	1
61821410	PC 20 / 1	200	1
61821420	PC 20 / 2	200	1
61821430	PC 20 / 3	200	1
61821440	PC 20 / 4	200	1
61821450	PC 20 / 5	200	1
61821460	PC 20 / 6	200	1
61821470	PC 20 / 7	200	1
61821480	PC 20 / 8	200	1
61821490	PC 20 / 9	200	1
61821500	PC 20 / blank	200	1
61821510	PC 20 / A	200	1
61821520	PC 20 / B	200	1
61821530	PC 20 / C	200	1
61821540	PC 20 / D	200	1
61821550	PC 20 / E	200	1
61821560	PC 20 / F	200	1
61821570	PC 20 / G	200	1
61821580	PC 20 / H	200	1
61821590	PC 20 / I	200	1
61821600	PC 20 / J	200	1
61821610	PC 20 / K	200	1

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

Marking rings PC

Article number	Article designation	Markers / PU	PU
61821620	PC 20 / L	200	1
61821630	PC 20 / M	200	1
61821640	PC 20 / N	200	1
61821650	PC 20 / O	200	1
61821660	PC 20 / P	200	1
61821670	PC 20 / Q	200	1
61821680	PC 20 / R	200	1
61821690	PC 20 / S	200	1
61821700	PC 20 / T	200	1
61821710	PC 20 / U	200	1
61821720	PC 20 / V	200	1
61821730	PC 20 / W	200	1
61821740	PC 20 / X	200	1
61821750	PC 20 / Y	200	1
61821760	PC 20 / Z	200	1
61821770	PC 20 / /	200	1
61821780	PC 20 / .	200	1
61821790	PC 20 / ,	200	1
61821800	PC 20 / :	200	1
61821810	PC 20 / =	200	1
61821820	PC 20 / earth	200	1
61821860	PC 20 / +	200	1
61821870	PC 20 / -	200	1
61821880	PC 20 / ~	200	1
PC 30			
61821900	PC 30 / 0	200	1
61821910	PC 30 / 1	200	1
61821920	PC 30 / 2	200	1
61821930	PC 30 / 3	200	1
61821940	PC 30 / 4	200	1
61821950	PC 30 / 5	200	1
61821960	PC 30 / 6	200	1
61821970	PC 30 / 7	200	1
61821980	PC 30 / 8	200	1
61821990	PC 30 / 9	200	1

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

Marking rings PC

Article number	Article designation	Markers / PU	PU
61822000	PC 30 / blank	200	1
61822010	PC 30 / A	200	1
61822020	PC 30 / B	200	1
61822030	PC 30 / C	200	1
61822040	PC 30 / D	200	1
61822050	PC 30 / E	200	1
61822060	PC 30 / F	200	1
61822070	PC 30 / G	200	1
61822080	PC 30 / H	200	1
61822090	PC 30 / I	200	1
61822100	PC 30 / J	200	1
61822110	PC 30 / K	200	1
61822120	PC 30 / L	200	1
61822130	PC 30 / M	200	1
61822140	PC 30 / N	200	1
61822150	PC 30 / O	200	1
61822160	PC 30 / P	200	1
61822170	PC 30 / Q	200	1
61822180	PC 30 / R	200	1
61822190	PC 30 / S	200	1
61822200	PC 30 / T	200	1
61822210	PC 30 / U	200	1
61822220	PC 30 / V	200	1
61822230	PC 30 / W	200	1
61822240	PC 30 / X	200	1
61822250	PC 30 / Y	200	1
61822260	PC 30 / Z	200	1
61822270	PC 30 / /	200	1
61822280	PC 30 / .	200	1
61822290	PC 30 / ,	200	1
61822300	PC 30 / :	200	1
61822310	PC 30 / =	200	1
61822320	PC 30 / earth	200	1
61822360	PC 30 / +	200	1
61822370	PC 30 / -	200	1

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

Marking rings PC

Article number	Article designation	Markers / PU	PU
61822380	PC 30 / ~	200	1
PC 40			
61822400	PC 40 / 0	200	1
61822410	PC 40 / 1	200	1
61822420	PC 40 / 2	200	1
61822430	PC 40 / 3	200	1
61822440	PC 40 / 4	200	1
61822450	PC 40 / 5	200	1
61822460	PC 40 / 6	200	1
61822470	PC 40 / 7	200	1
61822480	PC 40 / 8	200	1
61822490	PC 40 / 9	200	1
61822500	PC 40 / blank	200	1
61822510	PC 40 / A	200	1
61822520	PC 40 / B	200	1
61822530	PC 40 / C	200	1
61822540	PC 40 / D	200	1
61822550	PC 40 / E	200	1
61822560	PC 40 / F	200	1
61822570	PC 40 / G	200	1
61822580	PC 40 / H	200	1
61822590	PC 40 / I	200	1
61822600	PC 40 / J	200	1
61822610	PC 40 / K	200	1
61822620	PC 40 / L	200	1
61822630	PC 40 / M	200	1
61822640	PC 40 / N	200	1
61822650	PC 40 / O	200	1
61822660	PC 40 / P	200	1
61822670	PC 40 / Q	200	1
61822680	PC 40 / R	200	1
61822690	PC 40 / S	200	1
61822700	PC 40 / T	200	1
61822710	PC 40 / U	200	1
61822720	PC 40 / V	200	1

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

Marking rings PC

Article number	Article designation	Markers / PU	PU
61822730	PC 40 / W	200	1
61822740	PC 40 / X	200	1
61822750	PC 40 / Y	200	1
61822760	PC 40 / Z	200	1
61822770	PC 40 / /	200	1
61822780	PC 40 / .	200	1
61822790	PC 40 / ,	200	1
61822800	PC 40 / :	200	1
61822810	PC 40 / =	200	1
61822820	PC 40 / earth	200	1
61822860	PC 40 / +	200	1
61822870	PC 40 / -	200	1
61822880	PC 40 / ~	200	1

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16