

NYY-J, NYY-O

Fixed installation, direct burial; PVC cable with different application areas


NYY-J, NYY-O, VDE, PVC-Starkstromkabel acc. HD 603 / VDE 0276-603, direct burial and building installation, fixed installation with various applications

Info

CPR: Article number choice under www.lappkabel.com/cpr

Standard cable for direct burial with different application areas

0,6/1,0 kV alternative to the PVC installation cable NYM



Suitable for outdoor use

Application range

Power and control cable for fixed installation in the following applications:

For indoor and outdoor use

Burial without additional, suitable underground protection according to VDE standard HD 603/VDE 0276-603 - Part 3-G (point 4) governing PVC cables for direct burial: normal minimum installation depth 0.6 m, but at least 0.8 m under roads

In concrete with a temperature below the maximum cable operating temperature of +70 °C according to the VDE standard HD 603/VDE 0276-603 - Part 3-G (point 4) governing PVC cables for direct burial

Product features

Flame-retardant according IEC 60332-1-2

Current rating according to HD 603/VDE 0276-603, Part 3-G, Table 14 (buried at +20 °C ground temperature according to HD 603/VDE 0276-603, Part 3-G, point 5) for routing underground and Table 15 (in the air at an air temperature of +30 °C according to HD 603/VDE 0276-603, Part 3-G, point 5) when used outdoors; but always taking into consideration corrections/reductions to the current rating that may be necessary according to VDE 0298-4, and VDE 0298-4 (also refer to the catalogue appendix T12) for installation in and on buildings

Maximum DC voltage to ground 1,8 kV according to HD 603 / DIN VDE 0276-603

Norm references / Approvals

HD 603/VDE 0276-603 (for 1 to 5 cores)

HD 627/VDE 0276-627 (as from 7 cores)

Last Update (17.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

NYY-J, NYY-O

Product Make-up

Bare copper wire conductor

Abbreviations "re", "rm", "se", "sm":

r = round conductor form;

s = sectorial conductor form;

e = single-wire conductor;

m = multi-wire conductor;

Core insulation: Based on PVC

Filling compound over the core assembly

Outer sheath: Based on PVC

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000057

ETIM 5.0 Class-Description: Low voltage power cable

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000057

ETIM 6.0 Class-Description: Low voltage power cable

Core identification code:

Up to 5 cores: colour-coded according to VDE 0293-308, refer to Appendix T9

From 6 cores: black with white numbers

Conductor stranding:

Single or multi-wire

Minimum bending radius:

Single-core: 15 x outer diameter

Multi-core: 12 x outer diameter

Nominal voltage:

U0/U: 0.6/1.0 kV

Test voltage:

4000 V

Protective conductor:

J = with GN-YE protective conductor

O = without protective conductor

Temperature range:

During installation: -5 °C to +50 °C

Fixed installation: -40 °C to +70 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: excluding copper. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

NYY-J, NYY-O

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
NYY-J				
1550030	1 x 25rm	13	240	380
1550038	1 x 35rm	14	336	447
1550032	1 x 50rm	15	480	650
1550033	1 x 70rm	17	672	864
1550037	1 x 185rm	25	1776	2080
15500013	3 x 1,5re	12	43	223
15500023	4 x 1,5re	13	58	256
15500033	5 x 1,5re	14	72	293
1550004	7 x 1,5re	15	101	360
1550005	10 x 1,5re	18	144	520
1550006	12 x 1,5re	19	173	560
1550084	14 x 1,5re	20	202	620
1550008	19 x 1,5re	22	274	760
1550009	24 x 1,5re	24	346	900
15500103	3 x 2,5re	13	72	272
15500113	4 x 2,5re	14	96	316
15500123	5 x 2,5re	15	120	323
1550013	7 x 2,5re	16	168	450
1550090	10 x 2,5re	20	240	630
1550091	12 x 2,5re	20	288	680
15500583	3 x 4re	15	115	373
15500203	4 x 4re	16	154	439
15500263	5 x 4re	17	192	510
15500593	3 x 6re	16	173	466
15500213	4 x 6re	17	230	547
15500273	5 x 6re	19	288	640
15500603	3 x 10re	18	288	629
15500223	4 x 10re	19	384	743
15500823	5 x 10re	21	480	899
15500233	4 x 16re	22	614	1039
15500833	5 x 16re	23	768	1240
15500713	3 x 25rm/16re	25	874	1595
15500243	4 x 25rm	27	960	1620

NYY-J, NYY-O

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
15500153	3 x 35sm/16re	27	1162	1718
15500753	4 x 35sm	27	1344	1916
15500163	3 x 50sm/25rm	31	1680	2383
15500253	4 x 50sm	31	1920	2639
15500173	3 x 70sm/35sm	33	2352	3196
15500763	4 x 70sm	35	2688	3576
15500183	3 x 95sm/50sm	38	3216	4271
15500773	4 x 95sm	40	3648	4746
15500723	3 x 120sm/70sm	41	4128	5281
15500783	4 x 120sm	43	4608	5813
15500733	3 x 150sm/70sm	46	4992	6408
15500793	4 x 150sm	48	5760	7263
15500743	3 x 185sm/95sm	50	6240	7909
15500803	4 x 185sm	53	7104	8905
1550206	1 x 16re	11	154	239
1550207	1 x 25rm	13	240	380
1550208	1 x 35rm	14	336	447
1550209	1 x 50rm	15	480	650
1550210	1 x 70rm	17	672	864
1550211	1 x 95rm	19	912	1132
1550212	1 x 120rm	21	1152	1405
1550213	1 x 150rm	22	1440	1710
1550214	1 x 185rm	25	1776	2080
1550215	1 x 240rm	27	2304	2669
1550216	1 x 300rm	30	2880	3305
15502003	2 x 1,5re	11	29	210
15502533	4 x 16re	22	614	1039