

N2XS2Y

PE medium voltage cable with copper conductor

N2XS2Y, VDE, PE medium voltage cable acc. VDE 0276-620, with copper conductor, for fixed installation

Info

3 voltage classes: 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV

With copper conductor



Suitable for outdoor use



Mechanical resistance



UV-resistant

Application range

Power and control cable for fixed installation in the following applications:

In water, in ground, outdoors and indoors

In cable trays for power stations, industry, and distribution networks

Burial without additional, suitable underground protection according to HD 620/VDE 0276-620 - Part 10-C (point 4): normal minimum installation depth 0.6 m, but at least 0.8 m under roads

Product features

Suitable for installation or operation under high mechanical stress due to the PE-sheath

Current rating according to HD 620/VDE 0276-620, Part 10-C, Table 7 (buried at +20 °C ground temperature according to HD 620/VDE 0276-620, Part 10-C, point 5) for routing underground and Table 8 (in the air at an air temperature of +30 °C according to HD 620/VDE 0276-620, Part 10-C, point 5) when used outdoors; but always taking into consideration corrections/reductions to the current rating that may be necessary according to VDE 0298-4, and VDE 0298-4 (also refer to the catalogue appendix T12) for installation in and on buildings

Norm references / Approvals

HD 620/ VDE 0276-620

Last Update (08.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

N2XS2Y

Product Make-up

Copper conductor

Abbreviation "rm":

r = round conductor form;

m = multi-wire conductor

Core insulation: Cross-linked Polyethylen (XLPE)

Screen made of copper wires with one or two copper bond counter spiral

Outer sheath: PE, black

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001140 ETIM 5.0 Class-Description: Medium voltage power cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001140 ETIM 6.0 Class-Description: Medium voltage power cable
Conductor stranding:	Multi-wire
Minimum bending radius:	Fixed installation: 15 x outer diameter
Nominal voltage:	U ₀ /U: 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV
Test voltage:	Depending on nominal voltage: 6/10 kV: 15 kV 12/20 kV: 30 kV 18/30 kV: 45 kV
Temperature range:	During installation: -40 °C to +70 °C Fixed installation: -40 °C to +90 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Aluminium price basis: excludes aluminium. Refer to catalogue appendix T17 for the application and definition of "Metal price basis" and "Metal index".

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

N2XS2Y

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
6/10 (12) kV				
38107786	1x35 RM/16	24	518	770
38001000	1X50 RM/16	25	662	900
1552070	1X70 RM/16	26	854	1123
38107787	1x70 RM/50	27	1238	1450
38107788	1x95 RM/16	28	1094	1384
38107789	1x120 RM/16	30	1334	1623
38107029	1X150 RM/25	31	1723	1966
38107790	1x185 RM/25	33	2059	2335
1550067	1X240 RM/25	35	2587	2885
38107791	1x300 RM/25	37	3163	3480
38107792	1x400 RM/35	41	4234	4381
38107793	1x500 RM/35	43	5194	5382
12/20 (24) kV				
1552068	1X35 RM/16	28	518	914
1552069	1X50 RM/16	29	662	1049
1552041	1X70 RM/16	31	854	1289
3828017	1X95 RM/16	32	1094	1554
38107794	1x120 RM/16	34	1334	1802
1552047	1X150 RM/25	35	1723	2153
38107795	1x185 RM/25	37	2059	2533
38107796	1x240 RM/25	39	2587	3096
38107797	1x300 RM/25	42	3163	3705
38107798	1x300 RM/35	42	3274	3800
38107799	1x400 RM/35	44	4234	4519
38107800	1x500 RM/35	47	5194	5647
38107801	1x630 RM/35	51	6442	7049
18/30 (36) kV				
3036224	1X50 RM/16	34	662	1260
38107802	1x70 RM/16	36	854	1656
38107803	1x95 RM/16	37	1094	1789
38107804	1x120 RM/16	39	1334	2048
38107805	1x150 RM/25	40	1723	2409
3028167	1X185 RM/25	42	2059	2802

N2XS2Y

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
38107806	1x240 RM/25	44	2587	3382
38107807	1x300 RM/25	47	3163	4009
38107808	1x400 RM/35	50	4234	4934
38107809	1x500 RM/35	53	5194	6009
38107810	1x630 RM/35	56	6442	7423