

## CHARGE M3 ---/T2C S

Charge charging cable with type 2 connector, length 5m as component of a charging station

### Info

For charging stations



e-Mobility



Suitable for outdoor use



Cold-resistant



Mechanical resistance



Oil-resistant



Robust



UV-resistant

### Benefits

Resistant to microbes

Resistant to oil, dust and water

Special cable design for a long service life

Flexible at low temperatures

Withstands high mechanical stress, in particular abrasion and sliding demands

### Application range

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## CHARGE M3 ---/T2C S

For installation in charging stations

### Product Make-up

Cable for 1-phase charging up to 20A: ÖLFLEX® Charge 3G2.5 mm<sup>2</sup>+1x0.5 mm<sup>2</sup>

Cable for 3-phase charging up to 20A: ÖLFLEX® Charge 5G2.5mm<sup>2</sup>+1x0.5mm<sup>2</sup>

Cable for 1-phase charging up to 32A: ÖLFLEX® Charge 3G6mm<sup>2</sup>+1x0,5mm<sup>2</sup>

Cable for 3-phase charging up to 32 A: ÖLFLEX® Charge 5G6mm<sup>2</sup>+1x0.5mm<sup>2</sup>

Type 2 connectors are injection moulded in two-components process for optimal ergonomics

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002839

ETIM 5.0 Class-Description: Accessories for battery/charger

Certifications:

according to VDE-AR-E2283-5

according to EN 61851-1

Temperature range:

Flexing: -30 °C to +50 °C

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Further colour combinations and lengths on request

**CHARGE M3 ---/T2C S**

Article number	Version	Effective length (mm)	Copper index kg/1.000 pieces	Weight (kg/1000 pieces)	PU
Cut off clean, charging cable, vehicle connector type 2 (Total length: effective length +1m straight)					
74880134	Charging: 1 phase 20A	5000	473	1280	1
74880135	Charging: 1 phase 20A	7000	627	1600	1
74880137	Charging: 3 phase 20A	5000	770	1840	1
74880138	Charging: 3 phase 20A	7000	1020	2360	1
74880141	Charging: 1 phase 32A	5000	1096	2160	1
74880142	Charging: 1 phase 32A	7000	1452	2800	1
74880145	Charging: 3 phase 32A	5000	1717	2900	1
74880146	Charging: 3 phase 32A	7000	2303	3820	1