

## SILVYN® EF

SILVYN® EF is a liquidtight conduit with interlocked profile and a grey PVC jacket



Mechanical resistance



Robust



Temperature-resistant



Waterproof

### Benefits

- Protects against liquids
- High-tensile
- Robust
- High crush-resistance
- Extra flexible

### Application range

- Mechanical engineering
- Plant engineering
- Transformer construction
- Railway applications
- Paper industry

### Product Make-up

- Spirally-wound heavy metal protective conduit with roughened profile
- Plastic outer sheath

### Note

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**SILVYN® EF**

PU = 10m (on request)

**Technical Data**

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001179 ETIM 5.0 Class-Description: Protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001179 ETIM 6.0 Class-Description: Protective metallic hose
On request:	Longer lengths on drums 10m coils are available upon request
Colour delivered:	Grey
Material:	Galvanized steel with PVC sheath
Temperature range:	-25 °C to +70 °C Short-term: up to +90 °C

**Note**

\* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.



**SILVYN® EF**

Article number	Nominal size	ID x OD mm	Bending radius (mm)	PU ring (m)
SILVYN® EF				
61722240	5/16"	10.1 x 14.4	65	50
61712470	3/8"	12.6 x 17.8	85	75
61712480	1/2"	16 x 21.1	110	60
61712490	3/4"	21 x 26.4	140	50
61712500	1"	26.5 x 33.1	170	30
61712510	1 1/4"	35.1 x 41.8	215	30
61712520	1 1/2"	40.3 x 47.8	250	15
61712530	2"	51.6 x 59.9	300	15

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16