ÖLFLEX® TRAIN HT 150 F 1,8kV

Single-core cable according to EN 50382-2 type F for high requirements in railway applications

ÖLFLEX® TRAIN HT 150 F 1,8kV - Single-core cable EN 50382-2 type F, 1,8/3kV, 150°C, for use in railways/rolling stock EN 45545: HL1-HL3

Info

Meets EN 50382-2 type F and
EN 45545-2
High temperature resistance: -40°C up to +150°C
Highly oil- and fuel-resistant



- Rail
- Good chemical resistance
- Flame-retardant
- Halogen-free
- Cold-resistant
- Mechanical resistance
- Oil-resistant
- Temperature-resistant
- UV-resistant

Benefits

©2024 Lapp Group - Technical changes reserved

ÖLFLEX® TRAIN HT 150 F 1,8kV

Good flexibility - easy installation with tight space requirements
Good chemical resistance please see Appendix T1
For high ambient temperatures
Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

Application range

For use in railway vehicles, for fixed and protected installation and applications where limited movement may occur
Suitable for wiring of control cabinets, distributors, converters, motors and batteries
Also applicable within oily environments and areas with increased ambient temperature

Product features

Fire behaviour according to EN/IEC:
- Halogen-free acc. to EN 60754-1
- No corrosive gases acc. to EN 60754-2
- No fluorine acc. to EN 60684-2
- No toxic gases acc. to EN 50305
- Low smoke density acc. to EN 61034-2
- Flame-retardant acc. to EN 60332-1-2
- No flame propagation acc. to
EN 60332-3-24 / EN 60332-3-25 /
EN 50305

Chemical properties:
- Oil resistant acc. to EN 50382-2
- Acid resistant acc. to EN 50382-2
- Alkali resistant acc. to EN 50382-2
- Ozone resistant acc. to EN 50382-2

Current rating according to EN 50355, appendix A

Norm references / Approvals

EN 50382-2 type F
EN 45545-2 HL1, HL2, HL3

Product Make-up

Tinned-copper strand, fine-wire
Insulation: Silicone rubber compound, type EI 111
Colour: Black

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000057 ETIM 5.0 Class-Description: Low voltage power cable
Conductor stranding:	Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5
Minimum bending radius:	Fixed installation: 3 x outer diameter Occasional flexing: 5 x outer diameter
Nominal voltage:	U_0/U AC 1.8/3 kV U_m AC 3,6 kV V_0 DC 2,7 kV
Test voltage:	6,5 kV AC; 15 kV DC
Temperature range:	-40 °C to +150 °C

Last Update (21.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

ÖLFLEX® TRAIN HT 150 F 1,8kV

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.
Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.
Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum
Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2024 Lapp Group - Technical changes reserved

ÖLFLEX® TRAIN HT 150 F 1,8kV

Article number	Number of cores and mm² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
15382000	1 X 1.5	6.8	14.4	57
15382001	1 X 2.5	7.3	24	69
15382002	1 X 4.0	7.8	38.4	86
15382003	1 X 6.0	8.4	57.6	100
15382004	1 X 10.0	9.3	96	150
15382005	1 X 16.0	10.4	153.6	219
15382006	1 X 25.0	11.8	240	305
15382007	1 X 35.0	13.1	336	394
15382008	1 X 50.0	14.7	480	540
15382009	1 X 70.0	16.5	672	725
15382010	1 X 95.0	18.5	912	961
15382011	1 X 120.0	20.2	1152	1182
15382012	1 X 150.0	21.8	1440	1438
15382013	1 X 185.0	23.6	1776	1760

Last Update (21.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.