

## SILVYN® LTP 45° M

SILVYN® LTPW-M is a nickel-plated brass conduit fitting that offers a protection degree up to IP66/67/68/69



### Benefits

High tensile strength  
Vibration protection  
High sealing performance

### Application range

In combination with protective conduit:  
SILVYN® LTP  
Applications with high mechanical stress  
Used in areas where liquids are present

### Product Make-up

Metric connection thread  
45° elbow, hexagonal collar  
Threaded sleeve  
Cap nut

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Certifications:	IEC EN 61386-23
Material:	Body: nickel-plated brass Seal: PA compression seal
Protection rating:	IP66 IP67 IP68 (5 bar)

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**SILVYN® LTP 45° M**

IP69

Temperature range:

-50°C to +135°C

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.



## SILVYN® LTP 45° M

Article number	Metric size	SW wrench size mm	Thread length mm	Suitable for SILVYN® LTP	Pieces / PU
SILVYN® LTP 45° M					
55510300	20 x 1.5/1	24.0	13	16	10
55510301	20 x 1.5/2	24.0	13	20	10
55510302	25 x 1.5	30.0	14	25	10
55510303	32 x 1.5	36.0	15	32	2
55510304	40 x 1.5	47.0	18	40	1
55510305	50 x 1.5	61.0	18	50	1
55510306	63 x 1.5	67.0	20	63	1

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16