
# TEC sealing cap

TEC sealing caps with adhesive coating inside can be used for insulating and sealing of cable splices.




- Good chemical resistance
- Halogen-free
- UV-resistant
- Waterproof

## Benefits

Secure sealing through thermoplastic adhesive coating on the inside
Good resistance to chemicals and solvents
Ensures high tensile strength and mechanical protection

## Application range

For sealing cable ends against the seepage of moisture and contaminants

## Technical Data

| | |
|---|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000218<br>ETIM 5.0 Class-Description: Heat-shrink end cap |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000218<br>ETIM 6.0 Class-Description: Heat-shrink end cap |
| General: | UV-resistant<br>Double-walled |
| Colour delivered: | Black |
| Material: | Cross-linked modified polyolefin, with thermoplastic adhesive coating inside<br>Halogen-free and silicone-free |
| Temperature range: | -55 °C to +100 °C<br>Shrink temperature: 135 °C |

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

# TEC sealing cap

**Note**

1. after shrinking +/- 10%; 2. after shrinking +/- 20%

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.


©2023 Lapp Group - Technical changes reserved

# TEC sealing cap

| Article number | Article description | H max. (mm) | H min. (mm) | J max. (mm) | Cable Ø (mm) | R* after shrinking (mm) | Panel thickness HW* (mm) | Pieces / PU |
|---|---|---|---|---|---|---|---|---|
| 61830000 | TEC 15/4,5 | 15 | 4.5 | 4 | 5 - 12 | 30 | 2 | 10 |
| 61830010 | TEC 25/9 | 25 | 9 | 6.5 | 10 - 22 | 50 | 2.3 | 10 |
| 61830020 | TEC 36/15 | 36 | 15 | 10.5 | 17 - 30 | 80 | 3 | 10 |
| 61830040 | TEC 55/25 | 55 | 25 | 16 | 28 - 47 | 130 | 3.3 | 10 |
| 61830050 | TEC 80/40 | 80 | 40 | 17 | 45 - 70 | 150 | 4 | 10 |
| 61830060 | TEC 102/60 | 102 | 60 | 26 | 68 - 90 | 140 | 4 | 10 |
| 61830070 | TEC 148/57 | 148 | 57 | 27 | 80 - 133 | 105 | 3.3 | 10 |


©2023 Lapp Group - Technical changes reserved