

SILVYN® MAXI PA

SILVYN® MAXI PA is a parallel corrugated conduit with large diameter



Good chemical resistance



Halogen-free



Robust

Benefits

Dimensionally stable
Flexible
Crush-resistant

Application range

Mechanical engineering
Public utilities
Moving applications
Outdoors

Product features

Halogen and cadmium-free
Abrasion-resistant
High resistance to oil, petrol, acids and other chemicals

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

Thick-walled corrugated polyamide 6 conduit

Last Update (08.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® MAXI PA

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001175 ETIM 5.0 Class-Description: Corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001175 ETIM 6.0 Class-Description: Corrugated plastic hose
On request:	Available in PA 12
Colour delivered:	Grey (RAL 7001) Black (RAL 9005), UV-resistant
Material:	PA 6 Halogen-free Fire behaviour according to UL 94 HB
Temperature range:	-40°C to +115°C short-term +150°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® MAXI PA

Article number	Nominal size	ID x OD mm	Bending radius (mm)	Suitable for SILVYN® AFG-PA/AFW-PA	PU ring (m)
SILVYN® MAXI PA grey					
61791150	70	66.5 x 79.2	170	70	10
61791160	95	91 x 106	225	95	10
SILVYN® MAXI PA black					
61791155	70	66.5 x 79.2	170	70	10
61791165	95	91 x 106	225	95	10

Last Update (08.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16