SILVYN® SPLIT COV-M

SILVYN® SPLIT COV is a divisable conduit fitting for subsequent installation with the divisible conduit SILVYN® SPLIT



Halogen-free

Assembly time

Temperature-resistant

UV-resistant

Benefits

Fast and easy assembly
Subsequent mountable conduit insertion

Application range

In combination with protective conduit:
SILVYN® SPLIT
Mechanical engineering
Electrical industry
Used in areas where cables and wires need to be protected after assembly

Product features

divisable counter nut with metric thread

Note

UV-resistant and weather-resistant

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

SILVYN® SPLIT COV-M

	plastic hose
Colour delivered:	Black (RAL 9005), UV-resistant
Material:	Halogen-free PA
Temperature range:	-40 °C to +120 °C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (31.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

SILVYN® SPLIT COV-M

Article number	Metric size	Suitable for SILVYN® SPLIT	Pieces / PU
SILVYN® SPLIT COV-M (counter nut not included)			
61806680	16 x 1.5	10	100
61806681	20 x 1.5	14	100
61806682	25 x 1.5	20	50
61806683	32 x 1.5	23	50
61806684	40 x 1.5	37	25
61806685	50 x 1.5	45	25

©2023 Lapp Group - Technical changes reserved