

SILVYN® KLICK 90° PG

SILVYN® KLICK 90° PG - angled PG threaded conduit fitting for SILVYN® RILL



Assembly time



Temperature-resistant



Variety of approval certifications

Benefits

- 90° elbow allows easy installation
- Fast assembly
- Easy to disassemble
- High-tensile
- High sealing performance

Application range

- In combination with protective conduit:
 - SILVYN® RILL PA 6
 - SILVYN® RILL PA 12
- For applications with limited space
- Rotating applications

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

- PG connection thread
- 90° elbow
- Body with inner sealing
- Upper part with snap-in sleeve

Last Update (21.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® KLICK 90° PG

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Colour delivered:	Grey (RAL 7031) Black (RAL 9011), UV-resistant
Material:	PA6 Halogen-free
Protection rating:	IP 68 IP 69
Temperature range:	-40 °C to +115 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® KLICK 90° PG

Article number	PG size	Thread length mm	Clear opening (mm)	For conduit with outer Ø (mm)	Suitable for SILVYN® RILL	Pieces / PU
SILVYN® KLICK 90° PG grey						
61801020	9	10	12	13	13	50
61801030	11	10	15.5	15.8	16	50
56000100	13.5	13	15.5	18.5	18	50
61801040	16	13	18	21.2	21	50
61801050	21	13	24	28.5	28	25
61801060	29	15	32	34.5	34	10
61801061	36	15	36.5	42.5	42	10
61801062	48	16	48.5	54.5	54	5
SILVYN® KLICK 90° PG black						
61801025	9	10	12	13	13	50
61801035	11	10	15.5	15.8	16	50
56000105	13.5	13	15.5	18.5	18	50
61801045	16	13	18	21.2	21	50
61801055	21	13	24	28.5	28	25
61801065	29	15	32	34.5	34	10

Last Update (21.02.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16