


## SILVYN® KSE

SILVYN® KSE - PG threaded conduit fitting with integrated EMC screening for SILVYN® RILL



Wide clamping range



Assembly time



Optimum strain relief



Interference signals



UV-resistant

### Benefits

- Fast assembly
- Additional cable strain relief
- Additional cable sealing
- Optimum screen connection (EMC)

### Application range

- In combination with protective conduit
- SILVYN® RILL PA 6
- SILVYN® RILL PA 12
- Used in areas where screened cables and wires need to have additional protection

### Product Make-up

- PG connection thread
- EMC cable gland
- Body with inner sealing
- Upper part with snap-in sleeve

Last Update (21.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® KSE

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Colour delivered:	Black (RAL 9005), UV-resistant
Material:	Polyamide Nickel-plated brass
Protection rating:	IP 68
Temperature range:	-40 °C to +115 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® KSE**

Article number	PG size	Clamping range in mm	SW 1/2 mm	Overall length mm	Thread length mm	For conduit with outer Ø (mm)	Suitable for SILVYN® RILL	Pieces / PU
SILVYN® KSE								
55001200	9	4 - 8	17 / 22	57	12	13	13	20
55001230	16	10 - 14	24 / 31	70	12	21.2	21	10
55001240	21	14 - 17.5	30 / 39	75	12	28.5	28	10

Last Update (21.02.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16