

## SILVYN® US-M EE

SILVYN® US-M is a nickel-plated brass conduit fitting that offers IP40 / IP54 / IP66 protection degree depending on the used conduit



Maximum vibration protection



Space requirement



Robust



Temperature-resistant

### Benefits

High tensile strength  
Space-saving  
Vibration protection  
All-purpose  
Fast and easy assembly

### Application range

In combination with protective conduit:  
SILVYN® FPS  
SILVYN® FD-PU  
Mechanical engineering  
Plant engineering

### Product features

Compact design

### Product Make-up

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® US-M EE

Metric connection thread  
Hexagonal collar  
Threaded sleeve  
Sealing element  
Cap nut

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Material:	Body: nickel-plated brass Sealing ring: TPE
Protection rating:	IP 54 (with SILVYN® FPS, FD-PU)
Temperature range:	-40°C to +125°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® US-M EE**

Article number	Metric size	Clear opening (mm)	Suitable for SILVYN® FPS/FD-PU	Pieces / PU
SILVYN® US-M for SILVYN® FPS / FD-PU				
55502601	10 x 1.0	6	10	50
55502602	12 x 1.5	9	14	50
55502603	16 x 1.5	11.5	17	50
55502604	20 x 1.5	14.5	21	50
55502605	25 x 1.5	19.5	27	25
55502606	32 x 1.5	26.5	36	25
55502607	40 x 1.5	35	45	20
55502608	50 x 1.5	45.5	56	10
55502609	63 x 1.5	45.5	56	10

Last Update (31.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16

## SILVYN® US-M EE

