

SILVYN® CNP NPT

SILVYN® CNP conduit gland is made of nickel-plated brass for use with SILVYN® CNP



Good chemical resistance



Corrosion-resistant



Mechanical resistance

Benefits

Flame-retardant
High tensile strength
For high mechanical stress
High chemical-resistance

Application range

Mechanical engineering
Robot-building
Vending machine construction
Exporters

Product Make-up

The basic body is made of cast steel with a galvanised surface. The inner sleeve is made of polyamide and accommodates the conduit. A special profile on the inner sleeve is pressed into the conduit by the union nut including O-ring and counter nut

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class-Description: Screw connection for protective metallic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001180

Last Update (16.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® CNP NPT

	ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Material:	Body: cast steel with zinc-plated surface Inner sleeve: PA
Protection rating:	IP 67
Temperature range:	-45°C to +105°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.



SILVYN® CNP NPT

Article number	Nominal size	SW wrench size mm	Overall length mm	Suitable for SILVYN® CNP	Pieces / PU
SILVYN® CNP NPT fitting					
55500400	1/2"	27	55	3/8"	1
55500410	1/2"	32	66	1/2"	1
55500420	3/4"	39	66	3/4"	1
55500430	1"	45	73	1"	1
55500440	1 1/4"	59	87	1 1/4"	1
55500450	1 1/2"	67	87	1 1/2"	1
55500460	2"	82	101	2"	1

Last Update (16.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16